

DERUNGS Triango 100-3. Operating light for ceiling mounting or optionally for wall ...

??? ?????: 1005230

4.190,00 €
????? ??????



??? ??????

DERUNGS Triango 100-3. Operating light for ceiling mounting or optionally for wall mounting. Light output: 100000lux/1m, adjustable colour temperature, focusable light field 18-28cm, dimmable, 3 different light colours selectable. When ordering, please state whether you want ceiling or wall installation (for ceiling installation, we also need information on the room height and whether there is a false ceiling). NEW

-> ????? ??? ?????? ??? ?????? <-

